

Smoke Alarm Skirt (Ø140mm diameter) Installation Instructions

For use with

BESMOKEYV2XL
BESMOKEYV2
BESMOKEYV2BK
BESMOKEY10

Skirt Instruction

When replacing larger diameter smoke alarms with the BESMOKEYV2, BESMOKEYV2BK, or BESMOKEY10, the skirt can be clipped onto the base plate before wiring or installation to the ceiling, to provide a clean solution to cover any dissimilar paint marks. The tabs can be pushed in place and rotated to lock the alarm in place with the skirt.

